

SLIP RESISTANCE

* PENDULUM TEST *

Sample Ref	Surface Finish	Surface Roughness Rz	Surface Temperature °C	Direction	Friction Test Value (mm/s)	
					Dry	Wet
P60026	Medium Coat	34.3	24	Along	30	23
				Across	40	33
P60024	Flaw Coat	64.7	24	Along	100	87
				Across	100	88

The TFL pendulum tester has a range of readings from 0 to 100, high values indicating good slip resistance. Guidance on the interpretation of results using the Pave 2 S&S is suggested by the UK Slip Resistance Group as follows:

Potential For Slip	Friction Test Value
High	0 to 24
Medium	25 to 35
Low	36 +